



# R&S®NGM200

## versus Keithley 2281S-20-6



### Key features

- ▶ Fast regulation of output voltage with minimum overshoot and very fast load recovery time
- ▶ Minimum residual ripple and noise to supply interference-free voltage to sensitive DUTs
- ▶ Acquisition rate of up to 500 ksample/s to capture extremely fast variations in voltage or current
- ▶ High accuracy and readings with up to 6½ digit resolution
- ▶ Two quadrants: operates as source and sink
- ▶ Battery simulation

Your benefit	Features
Optimized load recovery time with minimal overshoot	Featuring optimized load recovery time of < 30 µs, the R&S®NGM200 power supplies can handle abrupt load changes from a few µA to the ampere range without creating voltage drops or overshoots.
Low ripple and noise	Low ripple and noise make it possible to supply interference-free voltage to sensitive designs, such as complex semiconductors, and to support the development of power amplifiers and MMICs.
High-speed acquisition (FastLog functionality)	With an acquisition rate of up to 500 ksample/s, voltage and current results are available every 2 µs. On the R&S®NGM200, data acquisition can be performed on both channels in parallel.
Battery simulation	The battery simulator function of the R&S®NGM200 enables simulation of the actual battery output performance. Testing can be based on a selected battery model, while battery capacity, SoC and Voc can be set to any state to test the device under specific conditions



For prices and more information, visit:  
[www.rohde-schwarz.com/product/NGM200](http://www.rohde-schwarz.com/product/NGM200)

Parameter	R&S®NGM200	Keithley 2281S
Number of channels	1 / 2	1
Output voltage per channel	0 V to 20 V	0 V to 20 V
Max. output power per channel	60 W	120 W
Max. output current per channel	≤ 6 V output voltage: 6 A > 6 V output voltage: 3 A	6 A
Max. sink current per channel	3 A	1 A
Adjustable output impedance	-50 mΩ to 100 Ω	not specified
Voltage ripple and noise (20 Hz to 20 MHz)	< 500 µV (RMS) < 2 mV (peak-to-peak)	< 1 mV (RMS) < 6 mV (peak-to-peak)
Current ripple and noise (20 Hz to 20 MHz)	< 1 mA (RMS)	< 3 mA (RMS)
Load recovery time (20 mV)	< 30 µs	< 50 µs
Programming resolution	1 mV / 0.1 mA	1 mV / 0.1 mA
Max. readback resolution	10 µV / 10 nA	100 µV / 10 nA
Readback accuracy, voltage	20 V range: < 0.02 % + 2 mV 5 V range: < 0.02 % + 500 µV	< 0.02 % + 2 mV
Readback accuracy, current	10 A range: < 0.05 % + 250 µA 1 A range: < 0.05 % + 1 mA 100 mA range: < 0.05 % + 100 µA 10 mA range: < 0.05 % + 15 µA	10 A range: < 0.05 % + 250 µA 1 A range: < 0.04 % + 250 µA 100 mA range: < 0.04 % + 10 µA 10 mA range: < 0.04 % + 10 µA
Max. measurement speed	500,000 sample/s (2 µs)	6½ digit: 20 readings/s 3½ digit: 845 readings/s
Protection functions	OCP / OVP / OPP / OTP	OCP / OVP / OTP
Remote control interfaces	standard: USB / LAN optional: IEEE-488 (GPIB)	standard: USB / LAN / IEEE-488 (GPIB)
Display	5", 800 × 480 pixel WVGA, capacitive touchscreen	4.3", 480 × 272 pixel, TFT LCD
Dimensions (W × H × D)	222 mm × 97 mm × 436 mm	255 mm × 107 mm × 415 mm
Weight	7.1 kg / 7.3 kg	10.85 kg
Weight	7.4 kg	8.2 kg

## R&S®NGM200 series vs. Keithley 2281S



### R&S®NGM200 series

- ▶ Two instruments, one or two channels
- ▶ Output power: 60 W per channel
- ▶ Output voltage: 0 V to 20 V per channel
- ▶ Available worldwide

### Keithley 2281S:

- ▶ Single-channel instrument
- ▶ Output power: 120 W
- ▶ Output voltage: 0 V to 20 V
- ▶ Max. sink current: 1 A



## Display size


### R&S®NGM200 series

The 5" display with 800 × 480 pixel resolution makes it easy to read results even from a distance. Information such as power values and statistics can be displayed in addition. Icons indicate the status of selected protection and special functions.




### Keithley 2281S:

4.3" display with 470 × 272 pixel resolution; capability to generate graphs.



## Source and sink and 6½ digit resolution



A resolution of up to 6½ digits is perfect for characterizing DUTs that have low power consumption in standby mode and high current in full load operation. The R&S®NGM200 power supplies automatically switch between source and sink mode. A negative current reading indicates that the instrument operates as a load.

## Battery simulation

### R&S®NGM200 series:



- ▶ **Discharging tests:** Based on a selected battery model, the battery capacity, SoC and Voc can be set to any state.
- ▶ **Charging tests:** Similar to discharging tests; here, the R&S®NGM200 operates in sink mode.
- ▶ **Dynamic simulation:** Voc, ESR and SoC change according to charging/discharging conditions like a real battery. SoC is shown graphically; other values numerically.

### Keithley 2281S:



- ▶ **Discharging and charging tests:** similar to R&S®NGM200.
- ▶ **Single-channel instrument:** The Keithley 2281S can run a charging or a discharging test, while the R&S®NGM200 can run both tests in parallel using the second channel.
- ▶ **Graphs:** Built-in graph function simplifies analyzing trends and displaying voltage and current waveforms.

## Large touchscreen – new standard for power supplies



The large capacitive touchscreen is the central operating element on the R&S®NGM200. Lightly tapping a numerical value will display a virtual keyboard to enter the desired value. Alternatively, the rotary knob can be used to set voltage and current values as well as limits for the various protection functions.